



3/4 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position Connector

By Raco
Catalog # 4733-8



3/4 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position Connector

*Representative Image

Features

- All gray nonmetallic construction provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- SWIVEL-LOK, multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating need to stock other angle connectors
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Application	For use in dry or wet locations when the conduit and fittings are not subject to physical damage Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance
Conduit Type	Liquidtight
Connector Type	SWIVEL-LOK
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169047330

Dimensions

Dimensions	3.66 in x 1.53 in x 1.53 in
Height	1.53 in
Length	3.66 in
Trade Size	3/4 in
Weight	0.127 lb
Width	1.53 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	4320

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Product Logo - LT COND](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-47338-SPEC-EN | REV 6/2024