



1 in. SWIVEL-LOK® Series, Type B Liquidtight Multi-Position Connector

By RACO
Catalog # 4734

1 in. SWIVEL-LOK®, Type B Liquidtight Multi-Position Connector



*Representative Image

Features

- All gray nonmetallic construction provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- SWIVEL-LOK, multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating need to stock other angle connectors
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

Application

For use in dry or wet locations when the conduit and fittings are not subject to physical damage; Use Type B conduit and fittings whenever flexibility is required for installation, operation, or maintenance

Specifications

Certified Listed	• UL Listed • CSA Certified
Environmental Conditions	Wet Location
Nema Rating	NEMA 4X, 12 and 13
Industry Standard(s)	UL 514B

Configuration

Connector Type	SWIVEL-LOK
----------------	------------

Dimensions

Length	4 in
Trade Size	1 in
Weight	0.12 lb.
Height	1.8 in
Width	1.8 in
Dimensions	4 in x 1.8 in x 1.8 in

General

Conduit Type	Liquidtight
Series	SWIVEL-LOK® Series
Fitting Type	Connectors
UPC	050169947340
Material	Nylon

Logistics

Minimum Pack Quantity	10
Pallet Quantity	2880
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)