



3/8 in. SWIVEL-LOK®, Extra Flexible Tubing Liquidtight Straight Connector

By Raco
Catalog # 4741



*Representative Image

3/8 in. SWIVEL-LOK®, Extra Flexible Tubing Liquidtight Straight Connector

Features

- All black nonmetallic construction ends metal fatigue and separation problems and provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- Additional sizes available

Application

- For use in dry or wet locations when the conduit and fittings are not subject to physical damage
- Use extra flexible tubing and connectors whenever added flexibility is required for installation, operation, or maintenance

General

Conduit Type	Liquidtight
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169047415

Dimensions

Dimensions	1.63 in x 1.14 in x 1.14 in
Height	1.14 in
Length	1.63 in
Trade Size	3/8 in
Weight	0.012 lb
Width	1.14 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT COND](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-4741-SPEC-EN | REV 6/2024