



# 3/4 in. SWIVEL-LOK®, Extra Flexible Tubing Liquidtight Straight Connector

By Raco  
Catalog # 4743

3/4 in. SWIVEL-LOK®, Extra Flexible Tubing Liquidtight Straight Connector

## Features

- All black nonmetallic construction ends metal fatigue and separation problems and provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- Additional sizes available

## Application

- For use in dry or wet locations when the conduit and fittings are not subject to physical damage
- Use extra flexible tubing and connectors whenever added flexibility is required for installation, operation, or maintenance

## General

Catalog Number	4743
Conduit Type	Liquidtight
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Nylon
UPC	050169047439

## Dimensions

Dimensions	2.22 in x 1.53 in x 1.53 in
Height	1.53 in



\*Representative Image

Length	2.22 in
Trade Size	3/4 in
Weight	0.08 lb
Width	1.53 in

## Certifications And Compliance

Buy American Compliant	Yes
Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li><li>• TAA Compliant (All status valid till December 2024)</li></ul>
Industry Standard(s)	UL 514B
Nema Rating	NEMA 4X, 12 and 13

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7200

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Product Logo - LT COND](#)  
[SDS - HCC SDS](#)  
[Specifications - 4743](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand