



Straight to 90° Extra Flexible Tubing SWIVEL LOK® Connector, Nylon

By Raco
Catalog # 4751



*Representative Image

Straight to 90° Extra Flexible Tubing SWIVEL LOK® Connector, Nylon

Features

- All black nonmetallic construction ends metal fatigue and separation problems and provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- SWIVEL-LOK, multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating need to stock other angle connectors
- Additional sizes available

General

Application	For use in dry or wet locations when the conduit and fittings are not subject to physical damage Use extra flexible tubing and connectors whenever added flexibility is required for installation, operation, or maintenance
Catalog Number	4751
Color	Black
Material	Nylon
UPC	050169047514

Dimensions

Dimensions	3.27 in x 1.3 in x 1.3 in
Height	1.3 in
Length	3.27 in
Trade Size	0.375 in
Weight	0.028 lb
Width	1.3 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Nema Rating	NEMA 4X, 12 and 13

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7200

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - LT COND](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-4751-SPEC-EN | REV 6/2024