



# Straight to 90° Extra Flexible Tubing SWIVEL LOK® Connector, Nylon

By Raco  
Catalog # 4753



\*Representative Image

Straight to 90° Extra Flexible Tubing SWIVEL LOK® Connector, Nylon

## Features

- All black nonmetallic construction ends metal fatigue and separation problems and provides superior corrosion resistance
- Each connector is supplied with a Neoprene O-ring and nylon gasket
- SWIVEL-LOK, multi-position connector (trade sizes 3/8 in. to 1 in.) twists from 0° to 90°, easing installation in difficult locations and eliminating need to stock other angle connectors
- Additional sizes available

## Application

- For use in dry or wet locations when the conduit and fittings are not subject to physical damage
- Use extra flexible tubing and connectors whenever added flexibility is required for installation, operation, or maintenance

## General

Catalog Number 4753  
Material Nylon  
UPC 050169047538

## Dimensions

Dimensions	3.66 in x 1.53 in x 1.53 in
Height	1.53 in
Length	3.66 in
Trade Size	0.75 in
Weight	0.09 lb
Width	1.53 in

## Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Nema Rating	NEMA 4X, 12 and 13

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	5000

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Product Logo - LT COND](#)  
[SDS - HCC SDS](#)  
[Specifications - 4753](#)  
[Terms and Conditions - HCC Terms & Conditions](#)