



## 3/4 in. Service Entrance Liquidtight UF Connector

By Raco  
Catalog # 4799-3



\*Representative Image

3/4 in. Service Entrance Liquidtight UF Connector

### Features

- Use a nylon connector when a lightweight corrosion resistant connection is required
- 3 #14, 3 #12, 3#10 UF wire
- Grommet opening: min., 0.20 in. x 0.60 in. - max., 0.26 in. x0.78 in
- Additional size available

### General

Accessory Type	Fitting
Catalog Number	4799-3
Conduit Type	Service Entrance
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Grommet Opening Maximum	.26 x .78 in
Grommet Opening Minimum	.20 x .60 in
Material	Nylon
UPC	050169479933

### Dimensions

Dimensions	2.15 in x 1.56 in x 1.56 in
Height	1.56 in
Length	2.15 in
Trade Size	3/4 in
Weight	0.112 lb
Width	1.56 in

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	4560

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Product Logo - SE CABLE](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-47993-SPEC-EN | REV 6/2024