



# 1/2 in. Hubs Form 2 Liquidtight Strain Relief Connector, Cable Range .062 - .125

By Raco  
Catalog # 4801-0



\*Representative Image

1/2 in. Hubs Form 2 Liquidtight Strain Relief Connector, Cable Range .062 - .125

## Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

## General

Catalog Number	4801-0
Color	Green
Color Code	Green
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480106

## Dimensions

Dimensions	1.65 in x 1.13 in x 1.13 in
Form Size	2 in
Height	1.13 in
Length	1.65 in
Trade Size	1/2 in

Weight	0.059 lb
Width	1.13 in

## Conductor Related

Cable Range	.062 - .125 in
-------------	----------------

## Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	12000

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Literature - Raco\\_Liquidtight\\_Diameter\\_Range\\_B60](#)
- [Product Logo - LT CORD](#)
- [SDS - HCC SDS](#)
- [Specifications - 4801-0](#)
- [Terms and Conditions - HCC Terms & Conditions](#)