



1/2 in. Hubs Form 1 Liquidtight Strain Relief Connector, Cable Range .375 - .437

By Raco
Catalog # 4801-5

1/2 in. Hubs Form 1 Liquidtight Strain Relief Connector, Cable Range .375 - .437

Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

General

Catalog Number	4801-5
Color	Blue
Color Code	Blue
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480151

Dimensions

Dimensions	0.88 in x 1.36 in x 1.36 in
Form Size	1 in
Height	1.36 in
Length	0.88 in



*Representative Image

Trade Size	1/2 in
Weight	0.059 lb
Width	1.36 in

Conductor Related

Cable Range	.375 - .437 in
-------------	----------------

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	12000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Literature - Raco_Liquidtight_Diameter_Range_B60](#)
[Product Logo - LT CORD](#)
[SDS - HCC SDS](#)
[Specifications - 48015](#)
[Terms and Conditions - HCC Terms & Conditions](#)