



1/2 in. Hubs Form 3 Liquidtight Strain Relief Connector, Cable Range .750 - .875

By Raco
Catalog # 4802-9

1/2 in. Hubs Form 3 Liquidtight Strain Relief Connector, Cable Range .750 - .875



*Representative Image

Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

General

Color	Purple
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480298

Dimensions

Dimensions	2.14 in x 1.38 in x 1.38 in
Form Size	3 in
Height	1.38 in
Length	2.14 in
Trade Size	1/2 in
Weight	0.139 lb
Width	1.38 in

Conductor Related

Cable Range	.750 - .875 in
-------------	----------------

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	4560

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Literature - Raco_Liquidtight_Diameter_Range_B60](#)
[Product Logo - LT CORD](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-48029-SPEC-EN | REV 6/2024