



3/4 in. Hubs Form 2 Liquidtight Strain Relief Connector, Cable Range .187 - .250

By Raco
Catalog # 4803-2



*Representative Image

3/4 in. Hubs Form 2 Liquidtight Strain Relief Connector, Cable Range .187 - .250

Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

General

Catalog Number	4803-2
Color Code	Red
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480328

Dimensions

Dimensions	2.05 in x 1.13 in x 1.13 in
Form Size	2 in
Height	1.13 in
Length	2.05 in
Trade Size	3/4 in
Weight	0.121 lb

Width 1.13 in

Conductor Related

Cable Range .187 - .250 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Division 2 • Class II Division 1 & 2 • Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7600

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Literature - Raco_Liquidtight_Diameter_Range_B60](#)
- [Product Logo - LT CORD](#)
- [SDS - HCC SDS](#)
- [Specifications - 4803-2](#)
- [Terms and Conditions - HCC Terms & Conditions](#)