



# 3/4 in. Hubs Form 2 Liquidtight Strain Relief Connector, Cable Range .500 - .625

By Raco  
Catalog # 4803-5

3/4 in. Hubs Form 2 Liquidtight Strain Relief Connector, Cable Range .500 - .625

## Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

## General

Catalog Number	4803-5
Color	Brown
Color Code	Brown
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480359

## Dimensions

Dimensions	2.05 in x 1.13 in x 1.13 in
Form Size	2 in
Height	1.13 in
Length	2.05 in



\*Representative Image

Trade Size	3/4 in
Weight	0.109 lb
Width	1.13 in

## Conductor Related

Cable Range	0.500 - 0.625 in
-------------	------------------

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7600

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Literature - Raco\\_Liquidtight\\_Diameter\\_Range\\_B60](#)  
[Product Logo - LT CORD](#)  
[SDS - HCC SDS](#)  
[Specifications - 4803-5](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand