



1 in. Hubs Form 4 Liquidtight Strain Relief Connector, Cable Range .375 - .500

By Raco
Catalog # 4804-0

1 in. Hubs Form 4 Liquidtight Strain Relief Connector, Cable Range .375 - .500



*Representative Image

Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

General

Color	Blue
Color Code	Blue
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480403

Dimensions

Dimensions	2.31 in x 1.75 in x 1.75 in
Form Size	4 in
Height	1.75 in
Length	2.31 in
Trade Size	1 in
Weight	0.231 lb
Width	1.75 in

Conductor Related

Cable Range	0.375 - 0.500 in
-------------	------------------

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3040

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Literature - Raco_Liquidtight_Diameter_Range_B60](#)
- [Product Logo - LT CORD](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-48040-SPEC-EN | REV 6/2024