



1 in. Hubs Form 4 Liquidtight Strain Relief Connector, Cable Range .875 - 1.000

By Raco
Catalog # 4804-4



*Representative Image

1 in. Hubs Form 4 Liquidtight Strain Relief Connector, Cable Range .875 - 1.000

Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

General

Catalog Number	4804-4
Color	Gray
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480441

Dimensions

Dimensions	2.31 in x 1.75 in x 1.75 in
Form Size	4 in
Height	1.75 in

Length	2.31 in
Trade Size	1 in
Weight	0.231 lb
Width	1.75 in

Conductor Related

Cable Range	.875 - 1.000 in
-------------	-----------------

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Hazardous Rating(s)	
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Literature - Raco_Liquidtight_Diameter_Range_B60](#)
- [Product Logo - LT CORD](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)