



# 1 in. Hubs Form 4 Liquidtight Strain Relief Connector, Cable Range 1.000 - 1.250

By Raco  
Catalog # 4804-5

1 in. Hubs Form 4 Liquidtight Strain Relief Connector, Cable Range 1.000 - 1.250

### Features

- Aluminum construction provides a corrosion resistant installation
- Innovative GOTHCA® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- GOTCHA® color-coded ring provides fast identification of cord size
- Additional colors and sizes available

### General

Catalog Number	4804-5
Color	Pink
Color Code	Pink
Conduit Type	Liquidtight
Connector Type	Strain-Relief
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Material	Aluminum
UPC	050169480458

### Dimensions

Dimensions	2.31 in x 1.75 in x 1.75 in
Form Size	4 in
Height	1.75 in
Length	2.31 in



\*Representative Image

Trade Size	1 in
Weight	0.231 lb
Width	1.75 in

### Conductor Related

Cable Range	1.000 - 1.250 in
-------------	------------------

### Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3040

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Literature - Raco\\_Liquidtight\\_Diameter\\_Range\\_B60](#)  
[Product Logo - LT CORD](#)  
[SDS - HCC SDS](#)  
[Specifications - 48045](#)  
[Terms and Conditions - HCC Terms & Conditions](#)