



3 in. x 2 in. Switch Box, Gangable, 2-1/4 in. Deep, One 1/2 in. KO & NMSC Clamps, TIGER GRIP®, Old Work

By Raco
Catalog # 487

3 in. x 2 in. Switch Box, Gangable, 2-1/4 in. Deep, One 1/2 in. KO & NMSC Clamps, TIGER GRIP®, Old Work



Features

- 3 in. x 2 in., 2-1/4 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Beveled corner boxes are designed to prevent the clamp screws from protruding into back wall
- 4 clamps designed for use with non-metallic sheathed cable
- Supplied with one 1/2 in. knockout
- Plaster ears and Tigergrip clips for "cut-in" or "old work" applications
- 10.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169004876
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.557 in
Cubic Capacity	10.5 cu.in
Depth	2.25 in
Height	4.24 in
Weight	0.574 lb
Width	2.525 in

Electrical Ratings

Power Distribution Features Fire Rated

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity 20
Packaging Type No Packaging
Pallet Quantity 2520

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-487-SPEC-EN | REV 6/2024