



1/2 in. Service Entrance Liquidtight UF Connector

By Raco
Catalog # 4899-9



1/2 in. Service Entrance Liquidtight UF Connector

*Representative Image

Features

- Rugged metallic construction will last the life of the installation.
- Grommet opening min: .20 in. x .40 in. max, .25 in. x .55 in
- Aluminum body construction will last the lifetime of the installation
- 1/2 in. trade size: 2 #14, 2 #12, 2#10 UF wire
- UL and CSA listed

General

Accessory Type	Fitting
Catalog Number	4899-9
Conduit Type	Service Entrance
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Grommet Opening Maximum	.25 x .55 in
Grommet Opening Minimum	.20 x .40 in
Material	Aluminum
UPC	050169489994

Dimensions

Dimensions	1.65 in x 1.25 in x 1.25 in
Height	1.25 in
Length	1.65 in
Trade Size	1/2 in
Weight	0.087 lb
Width	1.25 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	4800

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - SE CABLE](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-48999-SPEC-EN | REV 6/2024