



## 3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Eight 1/2 in. KO's, Plaster Ears

By RACO  
Catalog # [500](#)

3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Eight 1/2 in. KO's, Plaster Ears



### Features

- 3 in. x 2 in., 2-1/2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with eight 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### Specifications

Certified Listed	UL Listed
Buy American Compliant	No
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)

### Configuration

Knockouts	1/2 in
Bracket Type	No Bracket
Gangable	Yes

### Dimensions

Cubic Capacity	12.5 cu.in
Depth	2.5 in
Width	2 in
Weight	0.551 lb.
Height	4.219 in

### General

Wiring System	Conduit
Plaster Ears	Yes
Item Type	4D
Type	<ul style="list-style-type: none"> <li>• Switch Box</li> <li>• Box</li> </ul>
Fire Resistance	Yes
UPC	050169905005

### Logistics

Packaging Type	No Packaging
Carton Quantity	50
Pallet Quantity	3250

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)