



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Eight 1/2 in. KO's, Plaster Ears

By Raco
Catalog # 500



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Eight 1/2 in. KO's, Plaster Ears

Features

- 3 in. x 2 in., 2-1/2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for consult, NMSC, armored, metal clad, flex cable
- Supplied with eight 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	500
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Item Type	4D
Knockouts	1/2 in
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169905005
Wiring System	Conduit

Dimensions

Cubic Capacity	12.5 cu.in
Depth	2.5 in
Height	4.219 in
Weight	0.551 lb
Width	2 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	3250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Section E3 - Exothermic Grounding](#)
[Certifications - UL COC - E195978-17](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-500-SPEC-EN | REV 6/2024