



## 3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Four 1/2 & Two 3/4 in. KO's, TS Bracket

By Raco  
Catalog # 505

3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Four 1/2 & Two 3/4 in. KO's, TS Bracket



### Features

- 3 in. x 2 in., 2-1/2 in. deep
- Includes TS side-mount bracket with gauging tabs and recessed nailing spurs
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with four 1/2 in. and two 3/4 in. knockouts
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in.;3/4 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169005057
Wiring System	Conduit

### Dimensions

Cubic Capacity	12.5 cu.in
Depth	2.5 in
Height	7 in
Weight	0.636 lb
Width	2.203 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2100

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-17](#)  
[Certifications - UL COC - E195978- 9](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-505-SPEC-EN | REV 6/2024