



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Eight 1/2 in. KO's, Tigergrip, Old work, Plaster Ears

By Raco
Catalog # 506



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep, Eight 1/2 in. KO's, Tigergrip, Old work, Plaster Ears

Features

- 3 in. x 2 in., 2-1/2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with eight 1/2 in. knockouts
- Includes plaster ears and tiger grip clips for "cut-in" or "old work" applications
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	506
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169005064
Wiring System	Conduit

Dimensions

Actual Depth	2.55 in
--------------	---------

Cubic Capacity	12.5 cu.in
Depth	2.5 in
Height	4.219 in
Weight	0.579 lb
Width	2.5 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certified Listed	UL Listed

Logistics

Carton Quantity	16
Packaging Type	No Packaging
Pallet Quantity	2304

Product Assets

[360 Product View - RACO_506](#)
[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-17](#)
[Certifications - UL COC - E195978- 9](#)
[Sales Drawings - 506 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 506](#)
[Terms and Conditions - HCC Terms & Conditions](#)