



## Switch Box 2-1/2 in. Deep, Gangable with STAB-IT® Connector, Plaster Ears, 8 in. #12 Copper Pigtail

By Raco  
Catalog # 518S



Switch Box 2-1/2 in. Deep, Gangable with STAB-IT® Connector, Plaster Ears, 8 in. #12 Copper Pigtail

### Features

- 3 in. x 2 in., 2-1/2 in. deep
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Supplied with one 1/2 in. knockout
- Plaster ears allow a box to be used in "old work" applications
- Includes 8 in. #12 solid copper ground pigtail and STAB-IT® connector
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Application	RACO® STAB-IT boxes are great for any job where flexible armored cable is being used  RACO® Switch boxes are used to house wiring devices such as switches and outlets
Catalog Number	518S
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169500781

### Dimensions

Actual Depth	2.64 in
Cubic Capacity	12.5 cu.in
Depth	2.5 in
Height	4.223 in
Raised Ground	No
Weight	0.633 lb
Width	2.269 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Pallet Quantity	3150

### Product Assets

- [3D Models - 518S-3D](#)
- [Brochures - STAB-iT® Electrical Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - STAB-IT](#)
- [Sales Drawings - 518S Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® STAB-IT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: STAB-IT® with Cable Management](#)
- [Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-518S-SPEC-EN | REV 6/2024