



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep with One 1/2 in. KO & AC/MC/Flex Clamps, Griptite, Old Work

By Raco
Catalog # 523



3 in. x 2 in. Switch Box, Gangable, 2-1/2 in. Deep with One 1/2 in. KO & AC/MC/Flex Clamps, Griptite, Old Work

Features

- 3 in. x 2 in., 2-1/2 in. deep
- BX clamps provided for steel & alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Supplied with one 1/2 in. knockout
- Includes plaster ears and Griptite clips for "cut-in" or "old work" applications
- 12.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	Switch Box
	Box
UPC	050169005231
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Cubic Capacity	12.5 cu.in
Depth	2.5 in
Height	4.219 in
Weight	0.649 lb
Width	2.625 in

Electrical Ratings

Power Distribution Features Fire Rated

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-523-SPEC-EN | REV 6/2024