



3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Six 1/2 in. KO's, TS Bracket

By Raco
Catalog # 562

3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Six 1/2 in. KO's, TS Bracket



Features

- 3 in. x 2 in., 2-3/4 in. deep
- Includes TS side-mount bracket with gauging tabs and recessed nailing spurs
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for NMSC, armored, metal clad, flex cable
- Supplied with six 1/2 in. knockouts
- 14.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Catalog Number	562
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169005620
Wiring System	Conduit

Dimensions

Actual Depth	2.75 in
Cubic Capacity	14 cu.in
Depth	2.75 in
Height	7 in
Weight	0.707 lb
Width	2.203 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2100

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-21](#)
[Sales Drawings - 562 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-562-SPEC-EN | REV 6/2024