



## 3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Five 1/2 in. KO's & NMSC Clamps, TS Bracket

By Raco  
Catalog # 564

3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Five 1/2 in. KO's & NMSC Clamps, TS Bracket



### Features

- 3 in. x 2 in., 2-3/4 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Includes "TS" side-mount bracket with gauging tabs and recessed nailing spurs
- L clamps provided for non-metallic sheathed cable (NMSC)
- Supplied with five 1/2 in. knockouts
- 14 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Catalog Number	564
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169005644
Wiring System	Nonmetallic Sheathed Cable

### Dimensions

Actual Depth	2.96 in
Cubic Capacity	14 cu.in
Depth	2.75 in
Height	7 in
Weight	0.736 lb
Width	2.6 in

### Electrical Ratings

Power Distribution Features      Fire Rated

### Certifications And Compliance

Certified Listed      UL Listed

### Logistics

Carton Quantity      25  
Packaging Type      No Packaging  
Pallet Quantity      2100

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-21](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-564-SPEC-EN | REV 6/2024