



3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Two 1/2 in. & Six 3/4 in. KO's, Plaster Ears

By Raco
Catalog # 565

3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Two 1/2 in. & Six 3/4 in. KO's, Plaster Ears



Features

- 3 in. x 2 in., 2-3/4 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with two 1/2 in. and six 3/4 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 14.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in.;3/4 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169005651
Wiring System	Conduit

Dimensions

Cubic Capacity	14 cu.in
Depth	2.75 in
Height	4.219 in
Weight	0.597 lb
Width	2 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2750

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 7](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-565-SPEC-EN | REV 6/2024