



3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Seven 1/2 in. KO's & NMSC Clamps, Plaster Ears

By Raco
Catalog # 567



3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Seven 1/2 in. KO's & NMSC Clamps, Plaster Ears

Features

- 3 in. x 2 in., 2-3/4 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Cable clamps suitable for use with nonmetallic sheathed cable
- Supplied with seven 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 14.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169005675
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	3.086 in
Cubic Capacity	14 cu.in
Depth	2.75 in
Height	4.197 in
Weight	0.609 lb
Width	2.156 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-567-SPEC-EN | REV 6/2024