



3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Three 1/2 in KO's & AC/MC/Flex Clamps, TS Bracket

By Raco
Catalog # 574

3 in. x 2 in. Switch Box, Gangable, 2-3/4 in. Deep, Three 1/2 in KO's & AC/MC/Flex Clamps, TS Bracket



Features

- 3 in. x 2 in., 2-3/4 in. deep
- Includes "TS" side-mount bracket with gauging tabs and recessed nailing spurs
- BX clamps provided for steel & alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Supplied with five 1/2 in. knockouts
- 14 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169005743
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Cubic Capacity	14 cu.in
Depth	2.75 in
Height	7 in
Weight	0.784 lb
Width	2.203 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1375

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-21](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-574-SPEC-EN | REV 6/2024