



3 in. x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Nine 1/2 in. KO's, Plaster Ears

By Raco
Catalog # 590



3 in. x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Nine 1/2 in. KO's, Plaster Ears

Features

- 3 in. x 2 in., 3-1/2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with nine 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- 18.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	590
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Plaster Ears	Yes
Type	<ul style="list-style-type: none">• Switch Box• Box
UPC	050169905906
Wiring System	Conduit

Dimensions

Cubic Capacity	18 cu.in
Depth	3.5 in
Height	4.219 in
Weight	0.721 lb
Width	2 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certified Listed	UL Listed

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2250

Product Assets

[360 Product View - RACO_8590](#)
[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-18](#)
[Sales Drawings - 590 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 590](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand