



3 in x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Seven 1/2 in. KO's & NMSC Clamps, Plaster Ears, Ground Screw Driven

By Raco
Catalog # 601G



3 in x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Seven 1/2 in. KO's & NMSC Clamps, Plaster Ears, Ground Screw Driven

Features

- 3 in. x 2 in., 3-1/2 in. deep
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- L clamps provided for nonmetallic sheathed cable (NMSC)
- Supplied with seven 1/2 in. knockouts
- Includes plaster ears for "cut-in" or "old work" applications
- Ground screw driven
- 18 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	601G
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	Switch Box
	Box
UPC	050169506011
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Cubic Capacity	18 cu.in
Depth	3.5 in
Height	4.219 in
Weight	0.778 lb
Width	2 in

Electrical Ratings

Power Distribution Features Fire Rated

Certifications And Compliance

Certified Listed cULus Listed

Logistics

Carton Quantity 25
Packaging Type No Packaging
Pallet Quantity 2000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-601G-SPEC-EN | REV 6/2024