



3 in x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Three 1/2 in. KO's & AC/MC/Flex Clamps, TS Bracket

By Raco
Catalog # 604

3 in x 2 in. Switch Box, Gangable, 3-1/2 in. Deep, Three 1/2 in. KO's & AC/MC/Flex Clamps, TS Bracket



Features

- 3 in. x 2 in., 3-1/2 in. deep
- Includes TS side-mount bracket with gauging tabs and recessed nailing spurs
- BX clamps provided for steel & alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Supplied with seven 1/2 in. knockouts
- 18 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Catalog Number	604
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Ends Cable	4
Fire Resistance	Yes
Gangable	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box
	Box
UPC	050169006047
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Cubic Capacity	18 cu.in
Depth	3.5 in
Height	7 in
Weight	0.892 lb
Width	2.203 in

Electrical Ratings

Power Distribution Features Fire Rated

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity 25
Packaging Type No Packaging
Pallet Quantity 1650

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-21](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-604-SPEC-EN | REV 6/2024