



## 4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Ten 1/2 in. KO's, Raised Ground, Ground Screw Driven

By Raco  
Catalog # 611



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Ten 1/2 in. KO's, Raised Ground, Ground Screw Driven

### Features

- Made of pre-galvanized steel
- 4 in. x 2 in., 1-7/8 in. deep
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Popular for exposed work applications (surface mounting may require conduit)
- Supplied with ten 1/2 in. knockouts
- 13.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Catalog Number	611
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169006115
Wiring System	Conduit

### Dimensions

Cubic Capacity	13 cu.in
Depth	1.875 in
Height	4 in
Raised Ground	Yes
Weight	0.473 lb
Width	2.125 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	4000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-18](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978- 3](#)  
[Sales Drawings - 611 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-611-SPEC-EN | REV 6/2024