



Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Nickel Finish

By Raco
Catalog # [6239NI](#)



Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Nickel Finish

Features

- Can be used for power/data
- 15A, 125V tamper resistant receptacle
- Removable neoprene gaskets allow for independent use of either side of the receptacle with cover closed
- Recessed receptacle minimizes plug protrusion
- Height accessible adjustments after box is mounted

Application

- Carpet
- Tile
- Wood

General

| | |
|-------------------|--|
| Color | Nickel |
| Cover Shape | Round |
| Cover Type | Round |
| EU RoHS Indicator | Contact Manufacturer |
| Material | 6239NI |
| Number of Gang(s) | 1-Gang |
| Size | 1-Gang |
| Type | <ul style="list-style-type: none">• Boxes• Covers |
| Type of Use | Wood |
| UPC | 050169947142 |

Dimensions

| | |
|----------------|--------------------------------|
| Cubic Capacity | 28.0 cu.in |
| Dimensions | 5.813 in x 5.625 in x 5.938 in |
| Height | 5.938 in |
| Length | 5.813 in |
| Weight | 2.47 lb |
| Width | 5.625 in |

Certifications and Compliance

| | |
|------------------|---|
| Certified Listed | <ul style="list-style-type: none">• UL Listed• CSA Certified |
|------------------|---|

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 1 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 245 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Installation Manuals - 6239 Series Instruction Sheet](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Floor Boxes for Structural Wood Floors](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - How to Choose the Correct Floor Box](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
RACO-6239NI-SPEC-EN | REV 6/2023