



Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Stainless Steel Finish

By Raco
Catalog # [6239SS](#)



Single Gang Floor Box Kit with Recessed Duplex 15A TR Device and Adjustable Steel Box, Stainless Steel Finish

Features

- Can be used for power/data.
- 15A, 125V tamper resistant receptacle.
- Removable neoprene gaskets allow for independent use of either side of the receptacle with cover closed.
- Recessed receptacle minimizes plug protrusion.
- Height accessible adjustments after box is mounted.
- Three 1/2 in. knockouts
- Includes built in clamps for use with non-metallic sheathed cable
- 11.8 cu. in. capacity
- Maximum support load for a static light fixture is 50 lbs

Application

- Carpet
- Tile
- Wood

General

Color	Stainless Steel
Cover Shape	Round
Cover Type	Round
EU RoHS Indicator	Contact Manufacturer
Material	Steel
Size	1-Gang
Type	<ul style="list-style-type: none">• Boxes• Covers
Type of Use	Wood
UPC	050169947159

Dimensions

Cubic Capacity	28.0 cu.in
Dimensions	5.6 in x 5.6 in x 5.3 in
Height	5.3 in
Length	5.6 in
Weight	2.47 lb
Width	5.6 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
------------------	---

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	280

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Installation Manuals - 6239 Series Instruction Sheet](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Floor Boxes for Structural Wood Floors](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - How to Choose the Correct Floor Box](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
RACO-6239SS-SPEC-EN | REV 6/2023