



Switch Box 3-1/2 in. Deep, Gangable with STAB-IT® Connector, Plaster Ears, Old Work, GRIPTITE, 8 in. #12 Solid Copper Pigtail

By Raco
Catalog # 623S



Switch Box 3-1/2 in. Deep, Gangable with STAB-IT® Connector, Plaster Ears, Old Work, GRIPTITE, 8 in. #12 Solid Copper Pigtail

Features

- 3 in. x 2 in., 3-1/2 in. deep
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Supplied with five 1/2 in. knockouts
- Plaster ears allow a box to be used in "old work" applications
- Includes 8 in. #12 solid copper ground pigtail
- 18.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Application	RACO® STAB-IT boxes are great for any job where flexible armored cable is being used RACO® Switch boxes are used to house wiring devices such as switches and outlets
Catalog Number	623S
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169966235

Dimensions

Actual Depth	3.83 in
Cubic Capacity	18 cu.in
Depth	3.5 in
Height	4.22 in
Raised Ground	No
Weight	0.835 lb
Width	2.5 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Pallet Quantity	1750

Product Assets

- [3D Models - 623S-3D](#)
- [Brochures - STAB-iT® Electrical Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195978-18](#)
- [Product Logo - STAB-IT](#)
- [Sales Drawings - 623S Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® STAB-IT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-623S-SPEC-EN | REV 6/2024