



## Switch Box 3-1/2 in. Deep, Gangable with STAB-IT® Connector, TS Bracket, 1/2 in. Setback, 8 in. #12 Solid Copper Pigtail

By Raco  
Catalog # 624S



Switch Box 3-1/2 in. Deep, Gangable with STAB-IT® Connector, TS Bracket, 1/2 in. Setback, 8 in. #12 Solid Copper Pigtail

### Features

- 3 in. x 2 in., 3-1/2 in. deep
- Includes TS side-mount bracket with gauged tabs and recessed nailing spurs
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- Gangable switch boxes offer the option of constructing a box to hold two or more devices
- Supplied with five 1/2 in. knockouts
- Includes 8 in. #12 solid copper ground pigtail
- 18.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Application	RACO® STAB-IT boxes are great for any job where flexible armored cable is being used  RACO® Switch boxes are used to house wiring devices such as switches and outlets
Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Catalog Number	624S
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169966242

### Dimensions

Actual Depth	3.7 in
Cubic Capacity	18 cu.in
Depth	3.5 in
Height	7 in
Raised Ground	No
Weight	0.901 lb
Width	2.51 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Pallet Quantity	1125

### Product Assets

- [3D Models - 624S-3D](#)
- [Brochures - STAB-iT® Electrical Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Product Logo - STAB-IT](#)
- [Sales Drawings - 624S Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® STAB-IT](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-624S-SPEC-EN | REV 6/2024