



## 4 in. x 2 in. Handy Box, Welded, 1-1/2 in. Deep, Eleven 1/2 in. KO's

By Raco  
Catalog # 650

4 in. x 2 in. Handy Box, Welded, 1-1/2 in. Deep, Eleven 1/2 in. KO's



### Features

- Welded construction
- 4 in. x 2 in., 1-1/2 in. deep
- Supplied with eleven 1/2 in. knockouts
- 11.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Type	Box
UPC	050169906507
Wiring System	Conduit

### Dimensions

Actual Depth	1.563 in
Cubic Capacity	11.5 cu.in
Depth	1.5 in
Height	4 in
Raised Ground	No
Weight	0.471 lb
Width	2.125 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	5000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-8](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - 650](#)  
[Sales Drawings - RACO-welded-steel-box-infographic](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-650-SPEC-EN | REV 6/2024