



4 in. x 2 in. Handy Box, Welded, 1-1/2 in. Deep, Eleven 1/2 in. KO's, Ground Screw Driven

By Raco
Catalog # 650CSA



4 in. x 2 in. Handy Box, Welded, 1-1/2 in. Deep, Eleven 1/2 in. KO's, Ground Screw Driven

Features

- Welded construction
- 4 in. x 2 in., 1-1/2 in. deep
- Supplied with eleven 1/2 in. knockouts
- 11.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	650CSA
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Type	Box
UPC	050169506509
Wiring System	Conduit

Dimensions

Actual Depth	1.563 in
Cubic Capacity	11.5 cu.in
Depth	1.5 in

Height	4 in
Raised Ground	No
Weight	0.471 lb
Width	2.125 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed

Logistics

Carton Quantity	50
Packaging Type	No Packaging

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - UL COC - E195978- 8](#)
[Certifications - UL COC - E195978-8](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 650CSA Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 650CSA](#)
[Terms and Conditions - HCC Terms & Conditions](#)