



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Ten 1/2 in. KO's, Raised Ground

By Raco
Catalog # 660



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Ten 1/2 in. KO's, Raised Ground

Features

- Drawn construction
- 4 in. x 2 in., 1-7/8 in. deep
- Raised ground screw feature eliminates interference in surface mounting applications
- Supplied with ten 1/2 in. knockouts
- 13 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Drawn or Welded	Drawn
EU RoHS Indicator	Yes
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Type	<ul style="list-style-type: none">• Box• Box
UPC	050169906606
Wiring System	Conduit

Dimensions

Actual Depth	1.875 in
Cubic Capacity	13 cu.in
Depth	1.875 in
Height	4 in
Raised Ground	Yes
Weight	0.48 lb
Width	2.125 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	4000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[Sales Drawings - 660](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-660-SPEC-EN | REV 6/2024