



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Ten 1/2 in. KO's, Raised Ground

By RACO
Catalog # 660

4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Ten 1/2 in. KO's, Raised Ground



Features

- Drawn construction
- 4 in. x 2 in., 1-7/8 in. deep
- Raised ground screw feature eliminates interference in surface mounting applications
- Supplied with ten 1/2 in. knockouts
- 13 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

Specifications

Certified Listed	UL Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)

Configuration

Knockouts	1/2 in
Bracket Type	No Bracket

Dimensions

Cubic Capacity	13.0 cu.in
Depth	1.875 in

Actual Depth	1.875 in
Raised Ground	Yes
Width	2.125 in
Weight	0.48 lb.
Height	4 in

General

Wiring System	Conduit
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Drawn
UPC	050169906606

Logistics

Packaging Type	No Packaging
Carton Quantity	50
Pallet Quantity	4000

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)