



## 4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Seven 1/2 in. KO's, Raised Ground, A Bracket

By Raco  
Catalog # 661

4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Seven 1/2 in. KO's, Raised Ground, A Bracket



### Features

- Drawn construction with raised ground and "A" bracket which positions box against face and side of stud
- 4 in. x 2 in., 1-7/8 in. deep
- Supplied with seven 1/2 in. knockouts
- 13.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Setback	0.625
Bracket Type	A, for Metal or Wood Studs
Catalog Number	661
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Type	Box
UPC	050169006610
Wiring System	Conduit

### Dimensions

Actual Depth	1.88 in
Cubic Capacity	13 cu.in
Depth	1.875 in
Height	6.44 in
Raised Ground	Yes
Weight	0.648 lb
Width	2.96 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-18](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - 661 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-661-SPEC-EN | REV 6/2024