



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Eight 1/2 in. KO's, Raised Ground, TS Bracket

By Raco
Catalog # [662](#)



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Eight 1/2 in. KO's, Raised Ground, TS Bracket

Features

- Drawn construction with raised ground and "TS" side-mount bracket
- 4 in. x 2 in., 1-7/8 in. deep
- Supplied with eight 1/2 in. knockouts
- 13.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Type	Box
UPC	050169006627
Wiring System	Conduit

Dimensions

Actual Depth	1.875 in
Cubic Capacity	13 cu.in
Depth	1.875 in
Height	7.01 in
Raised Ground	Yes
Weight	0.601 lb
Width	2.59 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-21](#)
[Sales Drawings - 662](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-662-SPEC-EN | REV 6/2024