



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep with Seven 1/2 & One 3/4 in. KO's, Raised Ground

By Raco
Catalog # 666



4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep with Seven 1/2 & One 3/4 in. KO's, Raised Ground

Features

- Constructed of pre-galvanized steel with raised ground
- 4 in. x 2 in., 1-7/8 in. deep
- Popular for exposed work applications (surface mounting may require conduit)
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with seven 1/2 in. and one 3/4 in. knockouts
- 13.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;3/4 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169006665
Wiring System	Conduit

Dimensions

Actual Depth	1.875 in
Cubic Capacity	13 cu.in
Depth	1.875 in
Height	4 in
Raised Ground	Yes
Weight	0.473 lb
Width	2.125 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	4000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 3](#)
[Certifications - UL COC - E195978-18](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 666](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Sell Sheets - 2-in-1 Handy Box](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-666-SPEC-EN | REV 6/2024