



## 4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eleven 1/2 in. KO's

By RACO  
Catalog # 67ORAC

4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eleven 1/2 in. KO's



### Features

- Welded construction
- 4 in. x 2 in., 2-1/8 in. deep
- Supplied with eleven 1/2 in. knockouts
- 16.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### Specifications

Certified Listed	UL Listed
Buy American Compliant	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	<ul style="list-style-type: none"><li>• Buy America Compliant (All status valid till December 2025)</li><li>• Buy American Act Compliant (All status valid till December 2025)</li><li>• BABA Compliant (All status valid till December 2025)</li></ul>

### Configuration

Knockouts	1/2 in
Bracket Type	No Bracket
Number of Gang(s)	1-Gang

### Current

Power Distribution Features	Fire Rated
-----------------------------	------------

### Dimensions

Cubic Capacity	16.5 cu.in
Depth	2.125 in
Actual Depth	2.188 in
Raised Ground	No
Width	2.125 in
Weight	0.615 lb.
Height	4 in

### General

Wiring System	Conduit
Color	Gray
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Welded
UPC	050169906705

### Logistics

Packaging Type	No Packaging
Carton Quantity	50
Pallet Quantity	3200

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)