



## 4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eleven 1/2 in. KO's

By Raco  
Catalog # 670RAC

4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eleven 1/2 in. KO's



### Features

- Welded construction
- 4 in. x 2 in., 2-1/8 in. deep
- Supplied with eleven 1/2 in. knockouts
- 16.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Catalog Number	670RAC
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Yes
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169906705
Wiring System	Conduit

### Dimensions

Actual Depth	2.188 in
Cubic Capacity	16.5 cu.in
Depth	2.125 in
Height	4 in
Raised Ground	No
Weight	0.615 lb
Width	2.125 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	3200

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-8](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978- 8](#)  
[Sales Drawings - 670RAC Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-670RAC-SPEC-EN | REV 6/2024