



4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eight 1/2 in. KO's, A Bracket

By Raco
Catalog # 671

4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eight 1/2 in. KO's, A Bracket



Features

- Constructed of pre-galvanized steel with "A" bracket that positions box against face and side of stud
- 4 in. x 2 in., 2-1/8 in. deep
- With proper fitting can be used for conduit, NMSC, armored, metal clad, flex cable
- Supplied with eight 1/2 in. knockouts
- 16.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.625
Bracket Type	A, for Metal or Wood Studs
Catalog Number	671
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169006719
Wiring System	Conduit

Dimensions

Actual Depth	2.188 in
Cubic Capacity	16.5 cu.in
Depth	2.125 in
Height	6.438 in
Raised Ground	No
Weight	0.787 lb
Width	2.344 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 3](#)
[Certifications - UL COC - E195978-8](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 671 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-671-SPEC-EN | REV 6/2024