



4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eight 3/4 in. KO's

By Raco
Catalog # 674

4 in. x 2 in. Handy Box, Welded, 2-1/8 in. Deep, Eight 3/4 in. KO's



Features

- Welded construction
- 4 in. x 2 in., 2-1/8 in. deep
- Supplied with eight 3/4 in. knockouts
- 16.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	No Bracket
Catalog Number	674
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	3/4 in
Material	Steel
Number of Gang(s)	1-Gang
Type	Box
UPC	050169006740
Wiring System	Conduit

Dimensions

Actual Depth	2.2 in
Cubic Capacity	16.5 cu.in
Depth	2.125 in
Height	4 in
Raised Ground	No
Weight	0.612 lb
Width	2.11 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	3200

Product Assets

[3D Product View - RACO_674](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-8](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978- 8](#)
[Sales Drawings - 674 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-674-SPEC-EN | REV 6/2024