



4 in. Square Box, 2-Device Switch Box, Drawn, 2-1/8 in. Deep, Fourteen 1/2 in. KO's, TS Bracket

By Raco
Catalog # 681

4 in. Square Box, 2-Device Switch Box, Drawn, 2-1/8 in. Deep,
Fourteen 1/2 in. KO's, TS Bracket



Features

- Drawn construction with "TS" side-mount bracket
- 4 in. square, 2-1/8 in. deep
- Set back 1/2 in. eliminating the need for a plaster ring
- Supplied with fourteen 1/2 in. knockouts
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in
Material	Steel
Type	Box
UPC	050169006818
Wiring System	Conduit

Dimensions

Actual Depth	2.188 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	7 in
Raised Ground	No
Weight	0.926 lb
Width	4.375 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-9](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-681-SPEC-EN | REV 6/2024