



4 in. Square Box, 2-Device Switch Box, Drawn, 2-1/8 in. Deep, Three 1/2 & Eight 3/4 in. KO's, TS Bracket

By Raco
Catalog # 685SP

4 in. Square Box, 2-Device Switch Box, Drawn, 2-1/8 in. Deep,
Three 1/2 & Eight 3/4 in. KO's, TS Bracket



Features

- Drawn steel construction with "TS" side-mount bracket
- 4 in. square, 2-1/8 in. deep
- Set back 1/2 in. eliminating the need for a plaster ring
- Supplied with three 1/2 in. and eight 3/4 in. knockouts
- Acceptable for use in 2-hour fire rated walls

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Color	Gray
Drawn or Welded	Drawn
Fire Resistance	Yes
Knockouts	1/2 in.;3/4 in
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
Wiring System	Conduit

Dimensions

Actual Depth	2.208 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	6.992 in
Raised Ground	No
Weight	0.885 lb
Width	4.501 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	8
Packaging Type	No Packaging
Pallet Quantity	1152

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-685SP-SPEC-EN | REV 6/2024