



1-Gang Masonry Box, Gangable, 3-1/2 in. Deep, Ten TKO's

By Raco
Catalog # 689



1-Gang Masonry Box, Gangable, 3-1/2 in. Deep, Ten TKO's

Features

- Rugged welded design does not fall apart during construction.
- Gangable design allows installer to build unlimited number of gangs to hold multiple devices.
- Rectangular shape fits square cuts in block.
- Standard 1/2" and 3/4" TKO® knockouts.
- Device ears inside the box prevent mortar from getting in the device holes.
- Steel voltage partition #675 fits 2-1/2" and #676 fits 3-1/2" depth.
- Forward mounted grounding provision allows for easy installation of grounding pigtail.
- Standard wall plates can be used.
- Supplied with ten 1/2 and 3/4 in. concentric knockouts
- Gangable design allows construction of multiple gang box from one product
- Ground is located near the front of the box for installer's convenience
- 22.5 cu. in. capacity
- For 6, 8, and 10 in. block walls

General

Bracket Type	No Bracket
Catalog Number	689
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Gangable	Yes
Knockouts	1/2 in - 3/4 in Combination (TKO)
Material	Steel

Number of Gang(s)	1-Gang
Type	Box
UPC	050169006894
Wiring System	Conduit

Dimensions

Cubic Capacity	22.5 cu.in
Depth	3.5 in
Height	3.75 in
Weight	0.842 lb
Width	1.938 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certified Listed	UL Listed

Logistics

Carton Quantity	20
Packaging Type	No Packaging
Pallet Quantity	2000

Product Assets

[Catalogs - Steel Boxes, Covers and Accessories](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-18](#)
[Sales Drawings - 689 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 689](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand